

Emergency Wall Mounted Hand Operated Eye Wash

Product Code: 18-1004

Product Features

Compact, yet very efficient, this handy eye wash could save the day and someone's sight. Easy to activate it provides an immediate response in an emergency. Tip: it's recommended to flush the eyes for 15-20 minutes.

Robust and well-engineered the unit should be located within 10 seconds' walk from anywhere dangerous goods are used, stored, or transited through.

Replacement valve: 18-1014.

Assembly required.

Features

- Eye wash features Vertech™ Technology where dedicated eyewash and independently angled face wash streams deliver optimum coverage
- Zero velocity apex point provides more comfort and control for effective eye cleansing
- Easy to operate
- Complies with the requirements of ANSI Z358.1 and AS4775

Specifications

- Stainless steel bowl, and hand actuator
- Push activated eyewash with soft aerated flow and integral auto-open dust covers
- When activated, water will continuously flow through
- Integral flow volume control
- High visibility yellow powder coated push handle
- Weight: 6kgs
- Dimensions: 320 x 450 x 300mm (h,w,d)



Technical Information

Inlet connection:	15 mm (1/2") BSP with compression nut
Water supply line size:	Must be hydraulically sized to meet requirements.
Minimum performance requirements:	210 kPa. Caution should be taken when pressure exceeds 550 kPa (80 psi)
Minimum flow requirements:	1.5 lpm (0.4 US gpm)
Waste water outlet size:	G 1-1/2" BSP
Enware performance:	At working pressure: 210 kPa (30 psi) / Eyewash flow: 17lpm (4.5 US gpm)

Product Drawing



18-1004 | Emergency Wall Mounted Hand Operated Eye Wash

