

# Specification Sheet

## Emergency Pedestal Mounted Hand and Foot Operated Eye Wash

Product Code: 18-1005

### Product Features

This robust, hand and foot operated pedestal mounted eye wash is easy to operate and effectively flushes contaminants and irritants from the eyes.

Tip: We'd recommend installing the unit so there is an unobstructed path to it in the event of an emergency. Time is critical; and the first few seconds to reaching the eye wash can make all the difference to avoiding serious harm.

Replacement valve: 18-1014.

Assembly required.

### Features

- Free-standing (based must be affixed to the ground)
- Zero velocity apex point provides more comfort and control for effective eye cleansing
- Easy to operate
- Complies with the requirements of ANSI Z358.1 and AS4775

### Specifications

- Stainless steel bowl, and hand actuator
- Push and foot activated eyewash with soft aerated flow and integral auto-open dust covers
- When activated, water will continuously flow through
- Low-angle foot pedal for easy activation of eyewash
- High visibility yellow powder coated push handle and foot pedal
- Dimensions: 965mm (height from base to top of the bowl)
- Weight: 9kgs

### Technical Information

<b>Inlet connection:</b>	15 mm (1/2") BSP
<b>Water supply line size:</b>	Must be hydraulically sized to meet requirements.
<b>Minimum performance requirements:</b>	210 kPa. Caution should be taken when pressure exceeds 550 kPa (80 psi)
<b>Minimum flow requirements:</b>	17 lpm (4.5 US gpm)
<b>Waste water outlet size:</b>	38mm (1 1/2") OD
<b>Mounting base plate size:</b>	150 x 150 mm (5 9/10" x 5 9/10") with 4 bolt holes 11mm (7/16")

